

Detail & Submittal Sheet

Construction Specifications:

Titan Series Aluminum cabinets are constructed of non-extruded .063 thick aluminum with grey finish powder coat. All non-rated cabinets come standard with aluminum tubs, chrome steel handles and clear acrylic glazing. Fire-rated cabinets come standard with **steel tubs**, chrome steel handles and clear acrylic glazing.




To comply with **ADA Guidelines**, Extinguishers and Cabinets offer handles, brackets and turnbacks according to instructions provided by installer. For ADA compliance follow the specification ordering process dimensions in our catalog. Proper installation in accordance with the ADA Guidelines is the sole responsibility of the installer. For more information please visit the Accessibility Guidelines for Buildings and Facilities website or call them at 1-800-872-2253.

Project: _____
 Specification Reference: _____
 Model Number: _____ Quantity: _____
 Architect: _____
 Contractor: _____
 Distributor: _____
 Approved By: _____
 Date: _____

SPECIFICATION PROCESS: Follow the steps below to specify your cabinet. See detail legend on page 5.

- STEP 1: EXTINGUISHER SIZE:**
5 - 5 lb. 1 - 10 lb. 2 - 20 lb.
- STEP 2: CABINET STYLE:**
0 - Surface Mounted (S)
1 - Semi-Recessed (SR)
2 - Fully-Recessed (FR)
- STEP 3: DOOR STYLE:**
6 - Full Glass (FG)
7 - Full Metal (FM)
8 - Vertical Duo (VD)
- STEP 4: SERIES:**
TN - Aluminum Cabinet
- STEP 5: CABINET TYPE:**
SG - SAFEGUARD - Fire Rated with steel tub (see Fire Rated submittal)
- STEP 6: FINISH OPTIONS:**
AL - Aluminum Front (w/steel tub)
FAL - Full Aluminum (front and tub)
- STEP 7: HANDLE OPTIONS:**
008 - Safety Break Lock
010 - Alum. Die Cast Red "Fire" Handle
012 - ADA Handle
- STEP 8: GLAZING:**
G11 - Clear Acrylic (standard)
G12 - Clear Tempered Glass
- STEP 9: LETTERING:**
002 - Decal "Pull Firmly" R only
004 - Decal "Fire Ext." Lrg Vert R/B
005 - Decal "Fire Ext." Sm Horiz R/B

How to Measure a Cabinet



✓	Mod. #	Interior Tub Size			Overall Outside Trim		Rough Opening			Turnback	Accom. Ext Size Lbs.
		W	H	D	W	H	W	H	D		
Surface Mounted											
	506-TN	8"	17"	5"	10 3/4"	19 3/4"	-	-	-	-	5
	507-TN	8"	17"	5"	10 3/4"	19 3/4"	-	-	-	-	5
	508-TN	8"	17"	5"	10 3/4"	19 3/4"	-	-	-	-	5
	106-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	-	-	-	-	10
	107-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	-	-	-	-	10
	108-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	-	-	-	-	10
	206-TN	12"	27"	8"	16"	31"	-	-	-	-	20
	207-TN	12"	27"	8"	16"	31"	-	-	-	-	20
	208-TN	12"	27"	8"	16"	31"	-	-	-	-	20
Semi-Recessed											
	516-TN	8"	17"	5"	10 3/4"	19 3/4"	10"	19"	4 1/2"	1 3/4"	5
	517-TN	8"	17"	5"	10 3/4"	19 3/4"	10"	19"	4 1/2"	1 3/4"	5
	518-TN	8"	17"	5"	10 3/4"	19 3/4"	10"	19"	4 1/2"	1 3/4"	5
	116-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	9 3/4"	24 1/4"	3 1/2"	2 1/2"	10
	117-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	9 3/4"	24 1/4"	3 1/2"	2 1/2"	10
	118-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	9 3/4"	24 1/4"	3 1/2"	2 1/2"	10
	216-TN	12"	27"	8"	16"	31"	12 1/4"	27 1/4"	5"	3"	20
	217-TN	12"	27"	8"	16"	31"	12 1/4"	27 1/4"	5"	3"	20
	218-TN	12"	27"	8"	16"	31"	12 1/4"	27 1/4"	5"	3"	20
Fully-Recessed											
	526-TN	8"	17"	5"	12"	21"	8 1/4"	17 1/4"	4 3/4"	1/4"	5
	527-TN	8"	17"	5"	12"	21"	8 1/4"	17 1/4"	4 3/4"	1/4"	5
	528-TN	8"	17"	5"	12"	21"	8 1/4"	17 1/4"	4 3/4"	1/4"	5
	126-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	10"	24 1/4"	6 1/2"	1/4"	10
	127-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	10"	24 1/4"	6 1/2"	1/4"	10
	128-TN	9 1/2"	24"	6"	13 1/2"	28 1/2"	10"	24 1/4"	6 1/2"	1/4"	10
	226-TN	12"	27"	8"	16"	31"	12 1/2"	27 1/2"	8 1/4"	1/4"	20
	227-TN	12"	27"	8"	16"	31"	12 1/2"	27 1/2"	8 1/4"	1/4"	20
	228-TN	12"	27"	8"	16"	31"	12 1/2"	27 1/2"	8 1/4"	1/4"	20

Installation Options

